

ULTRA-K

Series 600K-*he*

High Efficiency, K-Rated Power Conditioning Transformer

5kVA – 25kVA

1 Phase General Specification

PART 1 - GENERAL

1.1 Description

This specification describes the design of a copper wound, multi-shielded, single phase, high efficiency, K-factor rated, power conditioning isolation transformer. The power conditioning transformer is a continuous duty rated, 600 volt class, convection cooled, dry type, isolation transformer designed to support harmonic rich non-linear loads while maintaining safe operating temperatures, and includes superior common and transverse mode noise attenuation. The power conditioning transformer meets and exceeds U.S. Department of Energy (DOE) 2016 high efficiency standards for applicable kVA ratings identified under DOE 10 CFR Part 431, and complies with the Canadian Energy Efficiency Standard C802.2-12.

1.2 Standards

The power conditioning system is designed in accordance with applicable portions of the following standards:

- A. U.S. Department of Energy (DOE) 2016 high efficiency standards identified under DOE 10 CFR Part 431
- B. Canadian Energy Efficiency Standard C802.2-12
- C. American National Standards Institute (ANSI C57.110 & C62.41-2002)
- D. Institute of Electrical and Electronic Engineers (IEEE 519-2014)
- E. National Fire Protection Association (NFPA) 70, National Electrical Code (NEC)
- F. Federal Information Processing Standards Publication 94 (FIPS Pub 94)
- G. UL Listed to Standard 1561
- H. C-UL listed to CSA Standard C22.2, No. 47-13
- I. RoHS compliant

PART 2 - PRODUCTS

2.1 Input Specifications

- A. Nominal AC input voltage ratings: 208 VAC, 240 VAC, 480 VAC or 600 VAC, 1 phase, with sufficient margin to sustain a constant input of +10% without saturation.
- B. The nominal operating frequency: 60 hertz \pm 5%.
- C. The power conditioning system's primary is configured single phase, two wire, plus ground, and includes full capacity taps at 2.5% increments, two (2) above and four (4) below the nominal voltage tap.
- D. Energizing inrush current will not exceed 10 times the full load input current for $\frac{1}{2}$ cycle.

2.2 Output Specifications

- A. Nominal AC output voltage ratings: 120 VAC, 120/240 VAC, or 208 VAC, single phase, 60 hertz. Special voltages available, consult factory.
- B. Output impedance: 3% typical.
- C. Harmonic k-rating: K-4, K-7, K-13, or K-20 rated in accordance with: $K = \sum I_h(\text{pu})^2 h^2$

2.3 Performance Specifications

- A. Load regulation: 2% typical, from no load to full load.
- B. Overload: Up to 500% for 10 seconds, 1000% for 1 cycle.
- C. THD: $\leq 1\%$ added to the output voltage waveform under a linear load.
- D. Output voltage: Sinusoidal with no flat topping when high crest factor (3.0 : 1), non-linear loads are present at the output.
- E. Audible noise measured at 1 meter from the unit: ≤ 45 dBA.
- F. Electrostatic shielding: Incorporates two, or an optional three, solid copper foil electrostatic shields which minimize inner winding capacitance and noise coupling between primary and secondary windings.
- G. Common mode noise attenuation: 126 dB with two shields, or 146dB with optional three shields.
- H. Transverse mode noise attenuation: 3 dB down at 10kHz, decaying 20 dB per decade.
- I. Efficiency: Meets and exceeds U.S. Department of Energy (DOE) 2016 high efficiency standards for applicable kVA ratings, 15kVA – 25kVA. All efficiency values are at 35% of nameplate-rated load with a transformer operating temperature of 75°C, determined according to the DOE Test Method for Measuring the Energy Consumption of Distribution Transformers under Appendix A to Subpart K of 10 CFR part 431.

Output kVA	ULTRA-K Efficiency @ 35% Load
5	> 95.70%
8	> 96.00%
10	> 96.20%
15	> 97.70%
20	> 97.85%
25	> 98.00%

2.4 Output Power Ratings, Dimensions and Weights

Output kVA	NEMA 2 Cabinet Dimensions (inches)	Weight (lbs.)	NEMA 3R Cabinet Dimensions (inches)	Weight (lbs.)
5	23"W x 20"D x 28"H	170	23"W x 24"D x 28"H	182
8	23"W x 20"D x 28"H	225	23"W x 24"D x 28"H	237
10	23"W x 20"D x 28"H	300	23"W x 24"D x 28"H	312
15	23"W x 20"D x 28"H	370	23"W x 24"D x 28"H	382
20	23"W x 20"D x 28"H	390	23"W x 24"D x 28"H	402
25	23"W x 20"D x 28"H	420	23"W x 24"D x 28"H	432

2.5 Main Transformer

- A. Transformer windings: All copper conductor construction, with separate primary and secondary isolated windings. The transformer conforms to NEC article 250 that specifies a separately derived power source.
- B. Copper bus connections are provided for isolated single phase output conductors, neutral conductor, and ground.
- C. All leads, wires and terminals are labeled to correspond with the circuit wiring diagram.
- D. Basic impulse level: No less than 10,000 Volts.
- E. MTBF: $\geq 200,000$ hours.
- F. Transformer steel: Grain oriented, M3 grade, silicon steel.
- G. Flux density: $\leq 15k$ gauss.
- H. Core losses: 0.2% to 0.4% of the kVA rating, model dependent.
- I. Insulation: Class N, 200°C with a maximum temperature rise above ambient of 115°C under a linear load, not exceeding 135°C under non-linear loading per UL 1561 standard.
- J. Cooling: Natural convection.

2.6 Cabinet

- A. Enclosure: NEMA type 2 general purpose, floor mounted, indoor enclosure is standard. Optional NEMA 3R enclosure is available.
- B. Construction: Cabinets are manufactured from 14 gauge steel with base sub-structure suitable for fork lifting. Galvanized steel is used to manufacture NEMA 3R enclosures.
- C. Paint: Baked on, powder coat paint finish with proper pre-treatment.
- D. Provisions exist to hardwire input and output to copper bus connections located behind the front panel of the transformer cabinet. Input and output landing locations are available on either side of the transformer cabinet. An optional lug kit is available containing mechanical (screw-type) lugs.

2.7 Environment

- A. Operating ambient temperature range: -25°C to +40°C.
- B. Humidity: 0 to 95% non-condensing.
- C. Altitude: Up to 5000 feet above sea level without de-rating.

2.8 Options

- A. Output Voltage Surge Protection Device (SPD):
 - 1. SPD with High Frequency Filter. The SPD is an integral, fused, single phase, secondary connected, transient voltage suppression network comprised of high energy metal oxide varistors with less than a 5 nanosecond response time and a maximum peak current handling capability of 40kA (8x20 μ sec) per mode. The suppression network will remain functional when subjected to ANSI/IEEE C62.41 Category B-3 waveforms. The SPD

includes a high frequency noise filter that increases the transverse mode noise attenuation to 3 dB down at 10kHz, decaying 40 dB per decade. A single status indicator light is provided to show that the SPD and filter are fully operational and functioning properly.

2. SPD with peak surge current capacity ratings from 50kA to 200kA per phase, UL 1449 4th Edition Listed, Type 2. The SPD has a nominal discharge current rating of 20kA, and a short circuit current rating (SCCR) of 200kA. Includes EMI/RFI filtering, Form C relay contacts rated for 2 amps at 30VDC or 250VAC, and LED protection status indicators.
- B. Main input or output circuit breaker: Molded case, 2 pole circuit breaker provided in a separate NEMA 1 enclosure for external mounting and installation.
 - C. High temperature / over temperature alarm contacts: Thermal warning alarm contacts provided for customer hardwired connection. Thermal sensors at 180°C and 200°C.
 - D. IR scanning window: Infrared transparent polymer IR window for safe routine thermal scanning of transformer connections under load, without exposing personnel to arc flash hazards (one 4" viewing window provided). Durable IR window is industrial-grade with a patented reinforced grill, is fully impact-resistant, and is UL and C-UL Listed.
 - E. NEMA 3R enclosure: UL listed NEMA 3R enclosure for outdoor installation. Enclosure is constructed using 14 gauge galvanized steel and provided with a durable powder coat paint finish.
 - F. Lug kit: Mechanical (screw-type) lugs shipped for installer convenience. Consult factory for number of conductors per lug and wire range.
 - G. Special designs: Special voltage configurations are available.

2.9 Warranty

Controlled Power Company warrants the Ultra-K, Series 600K-*he* transformer (core and coil) to be free from defects in material and workmanship for a period of 1 year full, and an additional 24 years prorated. All other unit components are covered by a 2 year full replacement warranty. The warranty periods begin following the original factory ship date.